

## PRODUCT DATA SHEET

Standing: 2024-03-21


LAUDA Varioshake VS 8 BE

Shaker 230 V; 50/60 Hz

Part Number: L003056

### Features

- Shaker with bidirectional motion, heavy-duty, low-noise in a compact design
- Electronic speed control, stepless, gentle start-up
- Clear control panel for easy operation with rotary knobs
- Timer adjustable up to 60 min. or continuous operation
- Shaking table made of anodized aluminum with four plastic pins
- Drive by an overload-protected AC motor
- Compact, low-wear mechanism with mass balancing for a secure stand
- Constant speed, independent of load
- Excellent for continuous use
- Outer housing made of electrolytically galvanized sheet steel, powder-coated



### Technical Features

Ambient temperature range	10 ... 60 °C
Shaking tray (WxD)	330 x 330 mm
Power consumption max.	0.07 kW
Shaking amplitude	20 mm
Shaking frequency	20 ... 300 1/min
Load max.	8 kg
Overall dimensions (WxDxH)	350 x 375 x 160 mm
Weight	11 kg
Power plug	Power cord with angled plug (CEE7/7)
Power supply	230 V; 50/60 Hz

Reserve technical changes

LAUDA DR. R. WOBSEY GMBH & CO. KG  
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0  
info@lauda.de • www.lauda.de  
WEEE-Reg.-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:  
LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
Sitz Lauda-Königshofen  
Registergericht Mannheim • HRB 560226

Geschäftsführer:  
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,  
Dr. Ralf Hermann, Dr. Marc Stricker  
Beirat: Dr. Gerhard Wobser