

## PRODUCT DATA SHEET

Standing: 2024-10-21

LAUDA Puridest PD 8 D

Water still 400 V; 3/N/PE; 50/60 Hz

Part Number: L003248

### Features

- Water Still (fully automatic) for double distillation, suitable for both bench and wall mounting
- Main switch with pilot lamp for the monitoring of both distillation stages at the front of the unit
- Valve made of Borosilicate glass 3.3 with PTFE plunger for single distillate
- Outlet with dust guard shield made of Borosilicate glass 3.3 for double distillate
- Condenser (cooling coil) 1st stage made of stainless steel
- Condenser (cooling coil) 2nd stage including the baffle made of DURAN® Borosilicate glass 3.3.
- Solenoid valve to control the water supply
- Economical energy consumption by distillation of the heated cooling water.
- Water saving through automatic water cut-off. Unnecessary water consumption will be avoided.
- Evaporator easily accessible for cleaning purposes.
- CO<sub>2</sub> degassing through outlet in the condenser.
- Electronic contamination monitoring of the still with distillation stop and visual cleaning instruction
- Electronic level control during the whole distilling process.
- Double-action low water cut-off through float switch and thermostatic safety switch.
- Heating element and evaporator made of stainless steel.
- Housing made of galvanised sheet steel, powder coated
- Double-walled housing



Reserve technical changes

### Options included

- With external level switch for monitoring the filling level of a separate storage tank

LAUDA DR. R. WOBSEY GMBH & CO. KG  
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0  
info@lauda.de • www.lauda.de  
WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:  
LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
Sitz Lauda-Königshofen  
Registergericht Mannheim • HRB 560226

Geschäftsführer:  
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,  
Dr. Marc Stricker  
Beirat: Dr. Gerhard Wobser

PRODUCT DATA SHEET

Standing: 2024-10-21

LAUDA Puridest PD 8 D  
Water still 400 V; 3/N/PE; 50/60 Hz  
Part Number: L003248

Technical Features

|                                        |                               |
|----------------------------------------|-------------------------------|
| Conductivity stage 1 /25 °C            | 2.2 µS/cm                     |
| Conductivity stage 2 /25 °C            | 1.6 µS/cm                     |
| Production output                      | 8 L/h                         |
| Heater power max.                      | 11.5 kW                       |
| Power consumption max.                 | 11.5 kW                       |
| Cooling water flow rate                | 3.3 L/min                     |
| Pressure difference cooling water min. | 3 bar                         |
| Maximal pressure cooling water         | 7 bar                         |
| Water cooling inlet for hose           | 1/2 "                         |
| Overall dimensions (WxDxH)             | 700 x 390 x 700 mm            |
| Weight                                 | 45 kg                         |
| Ambient temperature range              | 10 ... 40 °C                  |
| Power supply                           | 400 V; 3/N/PE; 50/60 Hz       |
| Power plug                             | Power cord without plug (HAR) |

Reserve technical changes