

## PRODUCT DATA SHEET

Standing: 2021-07-21

LAUDA Integral IN 1030 T Process thermostat  
 400 V; 3/PE; 50 Hz & 460 V; 3/PE; 60 Hz  
 Part Number: L002668

### Features

- Process thermostat with integrated cooling system for dynamic temperature control within external circuits
- Coloured TFT display for simultaneous indication of actual & set values and graphic illustration of the temperature profile
- Clear text menu navigation, six selectable languages DE, EN, FR, ES, IT, RU
- Management of heat transfer liquids with stored properties
- Easy input via cursor and soft keys. Additional Tmax key for overtemperature protection
- SelfCheck Assistant for system diagnosis
- Fully electronic continuous controller with PID action for internal & external control
- Self adapt function for determination of control parameters
- PowerAdapt system for the use of the maximum possible amount of heat permitted by the power supply system
- Low-level and adjustable over-temperature protection with acoustic alarm for use with flammable and non-flammable liquids
- Extremely powerful pressure pump
- Additional pump for internal circulation
- USB and Ethernet interface equipped as standard
- Port for external Pt100 integrated, second external Pt100 feasible via interface module
- Remote fault indication through floating contact
- Option for upgrading up to 2 additional interfaces (RS 232/485, Profibus, analogue, contact or EtherCAT module)
- Programmer with 150 temperature/time segments that can be separated into 5 programs
- Adjustable bypass for pressure limiting
- Digital display of pump pressure
- Integrated web server for browser based operation in local area networks via PC, tablet or smart phone, secure data transfer due to authentication procedure and encryption



Reserve technical changes

LAUDA DR. R. WOBSEY GMBH & CO. KG  
 Pfarrstraße 41/43 • 97922 Lauda-Königshofen  
 Postfach 1251 • 97912 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0 • F + 49 (0) 9343 503-222  
 info@lauda.de • www.lauda.de  
 WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
 Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:  
 LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
 Sitz Lauda-Königshofen  
 Registergericht Mannheim • HRB 560226

Geschäftsführer:  
 Dr. Gunther Wobser (Vors.), Dr. Mario Englert,  
 Dr. Marc Stricker  
 Beirat: Dr. Gerhard Wobser

## PRODUCT DATA SHEET

Standing: 2021-07-21

LAUDA Integral IN 1030 T Process thermostat  
400 V; 3/PE; 50 Hz & 460 V; 3/PE; 60 Hz  
Part Number: L002668

### Features

- SmartCool system for energy-saving digital cooling management including compressor on-off control
- Condenser cooling Air
- Utilises traditional refrigerants (HFCs) in accordance with European legislation to control F-gases (EU) 517/2014



Working temperature min.  
-30 °C



Working temperature max.  
150 °C

LAUDA DR. R. WOBSEY GMBH & CO. KG  
Pfarrstraße 41/43 • 97922 Lauda-Königshofen  
Postfach 1251 • 97912 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0 • F + 49 (0) 9343 503-222  
info@lauda.de • www.lauda.de  
WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:  
LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
Sitz Lauda-Königshofen  
Registergericht Mannheim • HRB 560226

Geschäftsführer:  
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,  
Dr. Marc Stricker  
Beirat: Dr. Gerhard Wobser

## PRODUCT DATA SHEET

Standing: 2021-07-21

LAUDA Integral IN 1030 T Process thermostat  
 400 V; 3/PE; 50 Hz & 460 V; 3/PE; 60 Hz  
 Part Number: L002668

### Technical Features (according to DIN 12876)

Working temperature range	-30 ... 150 °C
Ambient temperature range	5 ... 40 °C
Temperature stability	0.1 ± K
Heater power max.	8 kW
Power consumption max.	11 kW
Power consumption	16 A
Pump Pressure max.	5.5 bar (50 Hz); 7.0 bar (60 Hz)
Pump flow rate pressure max.	60 L/min (50 Hz); 70 L/min (60 Hz)
In / Outlet connection thread (outside)	M38x1,5
Inlet/outlet hose size	1 "
Filling volume min.	9.7 L
Filling volume max.	25.5 L
Overall dimensions (WxDxH)	760 x 650 x 1605 mm
Noise level	69 dB(A)
Refrigerant stage 1	R-449A (GWP 1397); 2.000 kg; 2.8 t CO <sub>2</sub> -eq
Power supply	400 V; 3/PE; 50 Hz & 460 V; 3/PE; 60 Hz
Power plug	Power cord with plug (IEC 60309, 5-pol, CEE, red, 16 A)

Reserve technical changes

LAUDA DR. R. WOBSEY GMBH & CO. KG  
 Pfarrstraße 41/43 • 97922 Lauda-Königshofen  
 Postfach 1251 • 97912 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0 • F + 49 (0) 9343 503-222  
 info@lauda.de • www.lauda.de  
 WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
 Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:  
 LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
 Sitz Lauda-Königshofen  
 Registergericht Mannheim • HRB 560226

Geschäftsführer:  
 Dr. Gunther Wobser (Vors.), Dr. Mario Englert,  
 Dr. Marc Stricker  
 Beirat: Dr. Gerhard Wobser

## PRODUCT DATA SHEET

Standing: 2021-07-21

LAUDA Integral IN 1030 T Process thermostat  
 400 V; 3/PE; 50 Hz & 460 V; 3/PE; 60 Hz  
 Part Number: L002668

Temperature	Heat transfer liquid	Cooling Capacity 50 Hz	Cooling Capacity 60 Hz
100 °C	Thermal oil	11 kW	11 kW
20 °C	Ethanol	11 kW	11 kW
10 °C	Ethanol	9.5 kW	9.5 kW
0 °C	Ethanol	7.1 kW	7.1 kW
-10 °C	Ethanol	4.9 kW	4.9 kW
-20 °C	Ethanol	3 kW	3 kW
-30 °C	Ethanol	1.6 kW	1.6 kW

Reserve technical changes

LAUDA DR. R. WOBSEY GMBH & CO. KG  
 Pfarrstraße 41/43 • 97922 Lauda-Königshofen  
 Postfach 1251 • 97912 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0 • F + 49 (0) 9343 503-222  
 info@lauda.de • www.lauda.de  
 WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
 Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:  
 LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
 Sitz Lauda-Königshofen  
 Registergericht Mannheim • HRB 560226

Geschäftsführer:  
 Dr. Gunther Wobser (Vors.), Dr. Mario Englert,  
 Dr. Marc Stricker  
 Beirat: Dr. Gerhard Wobser