

# PRODUCT DATA SHEET

Published: 2026-06-29

Metal hose

M16 x 1, temp. range: 10 ... 400 °C, 150 cm

Part Number: LZM 042

## Features

- Corrugated metal hose for temperature control with different heat transfer liquids
- Conical sealing
- Static bending radius: 50 mm; Dynamic bending radius: 180 mm
- Hose available by the metre



## Technical Features

|                              |                 |
|------------------------------|-----------------|
| Operating temperature range  | 10 ... 400 °C   |
| Connection 1 thread (inside) | M16 x 1         |
| Connection 2 thread (inside) | M16 x 1         |
| Length                       | 150 cm          |
| Inner diameters              | 10 mm           |
| Insulation thickness         | 1.6 mm          |
| Material                     | Stainless steel |

Reserve technical changes

LAUDA DR. R. WOBSEY GMBH & CO. KG  
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0  
info@lauda.de • www.lauda.de  
WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:  
LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
Sitz Lauda-Königshofen  
Registergericht Mannheim • HRB 560226

Geschäftsführer:  
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,  
Dr. Marc Stricker  
Beirat: Dr. Gerhard Wobser