

# PRODUCT DATA SHEET

Published: 2025-12-04

Pump link

M16 x 1, temperature range: 10 ... 400 °C

Part Number: LZM 044

## Features

- Conical sealing
- Static bending radius: 50 mm; Dynamic bending radius: 180 mm



## Technical Features

Operating temperature range

10 ... 400 °C

Connection 1 thread (inside)

M16 x 1

Connection 2 thread (inside)

M16 x 1

Length

25 cm

Material

Stainless steel

Reserve technical changes

LAUDA DR. R. WOBSEY GMBH & CO. KG  
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0  
info@lauda.de • www.lauda.de  
WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:  
LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
Sitz Lauda-Königshofen  
Registergericht Mannheim • HRB 560226

Geschäftsführer:  
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,  
Dr. Marc Stricker  
Beirat: Dr. Gerhard Wobser