

PRODUCT DATA SHEET

Published: 2026-06-29

Pump link

M16 x 1, temperature range: -90 ... 150 °C

Part Number: LZM 045

Features

- Conical sealing
- Insulation made of highly flexible, closed-cell insulating material based on EPDM.



Technical Features

Operating temperature range	-90 ... 150 °C
Connection 1 thread (inside)	M16 x 1
Connection 2 thread (inside)	M16 x 1
Length	25 cm
Inner diameters	10 mm
Insulation thickness	10 mm
Material	Stainless steel

Reserve technical changes

LAUDA DR. R. WOBSEY GMBH & CO. KG
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0
info@lauda.de • www.lauda.de
WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:
LAUDA DR. R. WOBSEY Verwaltungs-GmbH
Sitz Lauda-Königshofen
Registergericht Mannheim • HRB 560226

Geschäftsführer:
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,
Dr. Marc Stricker
Beirat: Dr. Gerhard Wobser