

PRODUCT DATA SHEET

Published: 2026-08-13

Metal hose

G 1" - G 1 1/4", temp. range: -50 ... 150 °C, 200 cm

Part Number: LZM 079

Features

- Insulation made of highly flexible, closed-cell insulating material based on EPDM.
- Flat sealing

Technical Features

Operating temperature range	-50 ... 150 °C
Connection 1 thread (inside)	G 1"
Connection 2 thread (inside)	G 1 1/4"
Length	200 cm
Insulation thickness	10 mm
Material	Stainless steel

Reserve technical changes

LAUDA DR. R. WOBSEY GMBH & CO. KG
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0
info@lauda.de • www.lauda.de
WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:
LAUDA DR. R. WOBSEY Verwaltungs-GmbH
Sitz Lauda-Königshofen
Registergericht Mannheim • HRB 560226

Geschäftsführer:
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,
Dr. Marc Stricker
Beirat: Dr. Gerhard Wobser