

## PRODUCT DATA SHEET

Published: 2026-06-29


Metal hose

M30 x 1,5, temp. range: -90 ... 150 °C, 300 cm

Part Number: LZM 089

### Features

- Conical sealing
- Insulating material for cold applications, closed-pore



### Technical Features

Operating temperature range	-90 ... 150 °C
Connection 1 thread (inside)	M30 x 1,5
Connection 2 thread (inside)	M30 x 1,5
Length	300 cm
Bending radius minimum/static	200 mm
Material inside	Stainless steel

Reserve technical changes

LAUDA DR. R. WOBSEY GMBH & CO. KG  
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0  
info@lauda.de • www.lauda.de  
WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:  
LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
Sitz Lauda-Königshofen  
Registergericht Mannheim • HRB 560226

Geschäftsführer:  
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,  
Dr. Marc Stricker  
Beirat: Dr. Gerhard Wobser