

PRODUCT DATA SHEET

Published: 2026-08-13

Silicone tube

ID 11 mm, insulation 19 mm

Part Number: LZS 009

Features

- Silicone hose with additional insulation for connection to pump nozzle with hose nipples
- "Silicone hoses are characterised by a unique combination of elasticity, purity and temperature resistance. They offer high temperature resistance as well as very good UV and ozone resistance."
- Silicone hoses are odourless and tasteless, largely chemically inert, and their inner wall is smooth, which minimises deposits and facilitates cleaning.
- The insulating material is weather-, UV- and ozone-resistant and is characterised by high water vapour diffusion resistance and low thermal conductivity.
- Can be used in the food and pharmaceutical industries due to their high purity.
- Silicone hoses not suitable for silicone oil
- Hose available by the metre



Technical Features

Operating temperature range	-60 ... 100 °C
Inner diameters	11 mm
Outer diameter	53 mm
Insulation thickness	19 mm
Material inside	Silicone
Material outside	EPDM

Reserve technical changes

LAUDA DR. R. WOBSEY GMBH & CO. KG
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0
info@lauda.de • www.lauda.de
WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:
LAUDA DR. R. WOBSEY Verwaltungs-GmbH
Sitz Lauda-Königshofen
Registergericht Mannheim • HRB 560226

Geschäftsführer:
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,
Dr. Marc Stricker
Beirat: Dr. Gerhard Wobser