

PRODUCT DATA SHEET

Standing: 2023-09-25

LAUDA Puridest PD 12 R

Water still 400 V; 3/N/PE; 50/60 Hz

Part Number: L003016

Features

- Water Still for single distillation (fully automatic) with storage tank, suitable for both bench and wall mounting
- The distillate storage tank accepts twice the hourly capacity of the still
- Distillate withdrawal through drain cock with continuous and touch position.
- Condenser (cooling coil) inside the storage tank, easily exchangeable.
- Solenoid valve to control the water supply
- Economical energy consumption by distillation of the heated cooling water.
- Water saving through automatic water cut-off. Unnecessary water consumption will be avoided.
- Evaporator easily accessible for cleaning purposes.
- CO₂ degassing through outlet in the condenser.
- Electronic contamination monitoring of the still with distillation stop and visual cleaning instruction
- Automatic refill of the storage tank after distillate removal, controlled by electronic level detection
- Thermostatic low water cut-off
- Heating element, evaporator, storage tank and condenser made of stainless steel.
- Housing made of galvanised sheet steel, powder coated
- Double-walled housing



Reserve technical changes

LAUDA DR. R. WOBSEY GMBH & CO. KG
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0
info@lauda.de • www.lauda.de
WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:
LAUDA DR. R. WOBSEY Verwaltungs-GmbH
Sitz Lauda-Königshofen
Registergericht Mannheim • HRB 560226

Geschäftsführer:
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,
Dr. Ralf Hermann, Dr. Marc Stricker
Beirat: Dr. Gerhard Wobser

PRODUCT DATA SHEET

Standing: 2023-09-25

LAUDA Puridest PD 12 R

Water still 400 V; 3/N/PE; 50/60 Hz

Part Number: L003016

Technical Features

Conductivity stage 1 /25 °C	2.3 µS/cm
Production output	12 L/h
Tank volume	24 L
Heater power max.	9 kW
Power consumption max.	9 kW
Cooling water flow rate	3.3 L/min
Pressure difference cooling water min.	3 bar
Maximal pressure cooling water	7 bar
Wasserkühlung Zulauf für Schlauch	1/2 "
Wasserkühlung Ablauf für Schlauch	3/4 "
Overall dimensions (WxDxH)	780 x 410 x 670 mm
Weight	40 kg
Ambient temperature range	10 ... 40 °C
Power supply	400 V; 3/N/PE; 50/60 Hz
Power plug	Power cord with plug (IEC 60309, 5-pol, CEE, red, 16 A)

Reserve technical changes

LAUDA DR. R. WOBSEY GMBH & CO. KG
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0
info@lauda.de • www.lauda.de
WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:
LAUDA DR. R. WOBSEY Verwaltungs-GmbH
Sitz Lauda-Königshofen
Registergericht Mannheim • HRB 560226

Geschäftsführer:
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,
Dr. Ralf Hermann, Dr. Marc Stricker
Beirat: Dr. Gerhard Wobser