

PRODUCT DATA SHEET

Standing: 2021-06-02

LAUDA Proline PJJ 12

Calibration therm. 230 V; 50/60 Hz

Part Number: L001925

Features

- Calibration thermostatic bath with latest microprocessor technology and installed cooling coil
- Easily readable green LED display for temperature
- User-friendly menu guidance with simplest 3-key operation
- EasyUse system for simple operation of the whole unit
- SelfCheck Assistant for system diagnosis
- Fully electronic continuous controller with PID action for internal & external control
- PowerAdapt system for the use of the maximum possible amount of heat permitted by the power supply system
- Low-level and adjustable over-temperature protection with acoustic alarm for use with flammable and non-flammable liquids
- LAUDA Varioflex pump (pressure) with 8 selectable levels
- Option for upgrading with up to 2 interfaces (RS 232/485, Profibus, analogue or contact modules, Ethernet-USB module)
- 2-chamber construction for constant level in the thermostating chamber
- Pump connectors on the side and in the back, installed bypass
- Bath from stainless steel (specially insulated for low-temperature work, with carrying handles and drain tap)
- For low temperatures an external cooling source is required



Reserve technical changes



Working temperature min.
30 °C



Working temperature max.
200 °C

LAUDA DR. R. WOBSEY GMBH & CO. KG
Pfarrstraße 41/43 • 97922 Lauda-Königshofen
Postfach 1251 • 97912 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0 • F + 49 (0) 9343 503-222
info@lauda.de • www.lauda.de
WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:
LAUDA DR. R. WOBSEY Verwaltungs-GmbH
Sitz Lauda-Königshofen
Registergericht Mannheim • HRB 560226

Geschäftsführer:
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,
Dr. Marc Stricker
Beirat: Dr. Gerhard Wobser

PRODUCT DATA SHEET

Standing: 2021-06-02

LAUDA Proline PJJ 12

Calibration therm. 230 V; 50/60 Hz

Part Number: L001925

Technical Features

Working temperature range	30 ... 200 °C
Working temperature range with external cooling	20 ... 200 °C
Operating temperature range	-40 ... 200 °C
Ambient temperature range	5 ... 40 °C
Temperature stability	0.01 ± K
Heater power max.	3.6 kW
Power consumption	16 A
Power consumption max.	3.7 kW
Pump Pressure max.	0.8 bar
Pump flow rate pressure max.	25 L/min
Bath volume min. / max.	8.5 / 13.5 L
Size of bath (ØxH)	120 x 320 mm
Overall dimensions (WxDxH)	220 x 360 x 574 mm
Power supply	230 V; 50/60 Hz
Power plug	Power cord with angled plug (CEE7/7)

Reserve technical changes

Standard accessories

- 1 Bath cover
- 4 screw caps, 4 closing plugs
- 2 nipples 13 mm for pump connectors
- 2 nipples for cooling coil

LAUDA DR. R. WOBSEY GMBH & CO. KG
Pfarrstraße 41/43 • 97922 Lauda-Königshofen
Postfach 1251 • 97912 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0 • F + 49 (0) 9343 503-222
info@lauda.de • www.lauda.de
WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:
LAUDA DR. R. WOBSEY Verwaltungs-GmbH
Sitz Lauda-Königshofen
Registergericht Mannheim • HRB 560226

Geschäftsführer:
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,
Dr. Marc Stricker
Beirat: Dr. Gerhard Wobser