

## PRODUCT DATA SHEET

Published: 2025-10-17

LAUDA Universa U 845 M

Cooling thermostat 100-125 V; 50/60 Hz

Part Number: L003874

### Features

- Bath circulation thermostat with advanced electronics ensures precise control accuracy
- Future-proof thanks to modularity: LAUDA Universa with interchangeable control head and heating/cooling base allows flexible adaptation to current and future requirements.
- Clear overview, intuitive operation: The 5-inch colour TFT display simultaneously shows temperature values with a progression graph, offers clear menu navigation in six languages and clear operating status icons - easily controlled via cursor and soft keys.
- Focus on safety: The dedicated Tmax button provides convenient access to the essential overtemperature protection setting during commissioning.
- Versatile pressure-suction pump: The LAUDA Varioflex pump, a powerful pressure-suction pump, offers eight selectable performance levels, adjustable flow rate distribution for internal/external circulation for optimal volume flow and pressure
- Ball bearing pump for extreme requirements: Guarantees safe operation with highly viscous and dense heat transfer fluids as well as with impurities in the temperature control bath.
- Easily accessible front switch on the control head allows the pump output to be adjusted during operation.
- Highly efficient refrigeration technology: Combination of speed-controlled inverter compressor and capacity control by means of electronic expansion valves and speed-controlled fans - for improved energy efficiency and reduced operating costs,
  - increased service life by avoiding frequent switch-on and switch-off cycles, - dynamic approach to the set temperature and
  - quieter operation.
- Adaptive bath edge ventilation (patent application): - Prevents icing and condensation - Stops water entering the bath - Blocks vapors to protect electronics. To increase operational safety and extend service life.
- Extensive functionality with programmer, safe mode, calibration options, controller self-adaptation and weekly planner for precise and flexible process control.
- Wireless communication: Integrated WLAN enables effortless connection with PC, tablet and smartphone.
- Intelligent remote control and monitoring: Integrated web server allows flexible remote control in the company network via the LAUDA Command app or browser-based, secured by PKI and 2-factor authentication. The connection to LAUDA.LIVE enables global, cloud-based data analysis and remote maintenance.



Reserve technical changes

LAUDA DR. R. WOBSEY GMBH & CO. KG  
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0  
info@lauda.de • www.lauda.de  
WEEE-Reg.-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:  
LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
Sitz Lauda-Königshofen  
Registergericht Mannheim • HRB 560226

Geschäftsführer:  
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,  
Dr. Marc Stricker  
Beirat: Dr. Gerhard Wobser

## PRODUCT DATA SHEET

Published: 2025-10-17

LAUDA Universa U 845 M

Cooling thermostat 100-125 V; 50/60 Hz

Part Number: L003874

### Features

- Maximum networking: Comprehensive connectivity for almost any application thanks to standard Ethernet, USB and interface for an external Pt100 as well as eleven optional interface modules.
- Comprehensive safety functions: - Effective over- and under-level protection - Adjustable overtemperature protection with acoustic alarm - Automatic system diagnostics at start-up with alarm and error message display - Smart temperature control media management with automatic limit value adjustment. For reliable operation and improved safety of your valuable samples.

### Options included

- Wi-Fi-certified devices may only be sold in the following countries: United States of America & Canada, EU including the UK and Switzerland, and India.



Working temperature min.  
-45 °C



Working temperature max.  
200 °C

LAUDA DR. R. WOBSEY GMBH & CO. KG  
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0  
info@lauda.de • www.lauda.de  
WEEE-Reg.-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:  
LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
Sitz Lauda-Königshofen  
Registergericht Mannheim • HRB 560226

Geschäftsführer:  
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,  
Dr. Marc Stricker  
Beirat: Dr. Gerhard Wobser

## PRODUCT DATA SHEET

Published: 2025-10-17

LAUDA Universa U 845 M

Cooling thermostat 100-125 V; 50/60 Hz

Part Number: L003874

### Technical Features

|                                         |                                                                                                                                                                                                                                                                |
|-----------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Working temperature range               | -45 ... 200 °C                                                                                                                                                                                                                                                 |
| Operating temperature range             | -45 ... 200 °C                                                                                                                                                                                                                                                 |
| Ambient temperature range               | 5 ... 40 °C                                                                                                                                                                                                                                                    |
| Temperature stability                   | 0.01 ± K                                                                                                                                                                                                                                                       |
| Heating capacity range                  | 1.4 ... 2.0 kW                                                                                                                                                                                                                                                 |
| Current max.                            | 16 A                                                                                                                                                                                                                                                           |
| Size of bath (W x D x H)                | 150 x 150 x 200 mm                                                                                                                                                                                                                                             |
| Bath opening (WxT)                      | 150 x 150 mm                                                                                                                                                                                                                                                   |
| Bath volume min. / max.                 | 5.0 / 8.0 L                                                                                                                                                                                                                                                    |
| Pump Pressure max.                      | 0,7 bar                                                                                                                                                                                                                                                        |
| Pump suction max.                       | 0,4 bar                                                                                                                                                                                                                                                        |
| Pump flow rate max. (pressure)          | 25 L/min                                                                                                                                                                                                                                                       |
| Pump Flow rate max. (suction)           | 23 L/min                                                                                                                                                                                                                                                       |
| In / Outlet connection thread (outside) | M16 x 1                                                                                                                                                                                                                                                        |
| In / Outlet Ø olives                    | 13 mm                                                                                                                                                                                                                                                          |
| Overall dimensions (WxDxH)              | 310 x 490 x 757 mm                                                                                                                                                                                                                                             |
| Weight                                  | 45 kg                                                                                                                                                                                                                                                          |
| Refrigerant stage 1                     | R-290 (GWP 3); 0.080 kg; 0.0 t CO <sub>2</sub> -eq                                                                                                                                                                                                             |
| Power supply                            | 100-125 V; 50/60 Hz                                                                                                                                                                                                                                            |
| Power plug                              | Power cord with plug (NEMA 5-20P)                                                                                                                                                                                                                              |
| Certification                           | NRTL according to UL 61010-1:2012/R:2023-06, UL 61010-2-011:2021, CSA C22.2 No. 61010-1:2012/U3:2023-06, CSA C22.2 No. 61010-2-011:2019 UL 61010-1:2012/R:2023-06, UL 61010-2-010:2019, CSA C22.2 No. 61010-1:2012/U3:2023-06, CSA C 22.2 No. 61010-2-010:2019 |

Reserve technical changes

LAUDA DR. R. WOBSEY GMBH & CO. KG  
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0  
info@lauda.de • www.lauda.de  
WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:  
LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
Sitz Lauda-Königshofen  
Registergericht Mannheim • HRB 560226

Geschäftsführer:  
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,  
Dr. Marc Stricker  
Beirat: Dr. Gerhard Wobser

# PRODUCT DATA SHEET

Published: 2025-10-17

LAUDA Universa U 845 M

Cooling thermostat 100-125 V; 50/60 Hz

Part Number: L003874



Power cord with plug (NEMA 5-20P)

| Temperature | Pump stage | Heat transfer liquid | Cooling Capacity 50 Hz | Cooling Capacity 60 Hz |
|-------------|------------|----------------------|------------------------|------------------------|
| 200 °C      | 8          | Thermal oil          | 0.8 kW                 | 0.8 kW                 |
| 100 °C      | 8          | Thermal oil          | 0.8 kW                 | 0.8 kW                 |
| 20 °C       | 8          | Ethanol              | 0.8 kW                 | 0.8 kW                 |
| 10 °C       | 8          | Ethanol              | 0.73 kW                | 0.73 kW                |
| 0 °C        | 8          | Ethanol              | 0.7 kW                 | 0.7 kW                 |
| -10 °C      | 8          | Ethanol              | 0.59 kW                | 0.59 kW                |
| -20 °C      | 4          | Ethanol              | 0.44 kW                | 0.44 kW                |
| -30 °C      | 4          | Ethanol              | 0.26 kW                | 0.26 kW                |
| -40 °C      | 4          | Ethanol              | 0.12 kW                | 0.12 kW                |
| -45 °C      | 4          | Ethanol              | 0.05 kW                | 0.05 kW                |

Reserve technical changes

## Standard accessories

- 1 Bath cover
- Pump connection set with M16x1 stainless steel connections
- 2 screw caps, 2 closing plugs
- 2 nipples 13 mm for pump connectors

LAUDA DR. R. WOBSEY GMBH & CO. KG  
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0  
info@lauda.de • www.lauda.de  
WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:  
LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
Sitz Lauda-Königshofen  
Registergericht Mannheim • HRB 560226

Geschäftsführer:  
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,  
Dr. Marc Stricker  
Beirat: Dr. Gerhard Wobser

## PRODUCT DATA SHEET

Published: 2025-10-17


LAUDA Universa U 845 M

Cooling thermostat 100-125 V; 50/60 Hz

Part Number: L003874

### COOLING PERFORMANCE Heat transfer liquid: Ethanol, bath closed

Bath temperature °C



- 1 U 845 M
- 2 U 2040 M
- 3 U 4230 M
- 4 U 855 M
- 5 U 1645 M
- 6 U 890 M

LAUDA DR. R. WOBSEY GMBH & CO. KG  
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0  
info@lauda.de • www.lauda.de  
WEEE-Reg.-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:  
LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
Sitz Lauda-Königshofen  
Registergericht Mannheim • HRB 560226

Geschäftsführer:  
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,  
Dr. Marc Stricker  
Beirat: Dr. Gerhard Wobser

## PRODUCT DATA SHEET

Published: 2025-10-17


LAUDA Universa U 845 M

Cooling thermostat 100-125 V; 50/60 Hz

Part Number: L003874

### PUMP CHARACTERISTIC Heat transfer liquid: Water

Pressure bar



Suction

Flow rate L/min

- 1 Stage 1
- 2 Stage 2
- 3 Stage 3
- 4 Stage 4
- 5 Stage 5
- 6 Stage 6
- 7 Stage 7
- 8 Stage 8

Reserve technical changes

LAUDA DR. R. WOBSEY GMBH & CO. KG  
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0  
info@lauda.de • www.lauda.de  
WEEE-Reg.-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:  
LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
Sitz Lauda-Königshofen  
Registergericht Mannheim • HRB 560226

Geschäftsführer:  
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,  
Dr. Marc Stricker  
Beirat: Dr. Gerhard Wobser