

## PRODUCT DATA SHEET

Published: 2026-07-21

LAUDA Universa U 8 M

Heating thermostat 100-125 V; 50/60 Hz

Part Number: L003871

### Features

- Bath circulation thermostat with advanced electronics ensures precise control accuracy
- Future-proof thanks to modularity: LAUDA Universa with interchangeable control head and heating/cooling base allows flexible adaptation to current and future requirements.
- Clear overview, intuitive operation: The 5-inch colour TFT display simultaneously shows temperature values with a progression graph, offers clear menu navigation in six languages and clear operating status icons - easily controlled via cursor and soft keys.
- Focus on safety: The dedicated Tmax button provides convenient access to the essential overtemperature protection setting during commissioning.
- Versatile pressure-suction pump: The LAUDA Varioflex pump, a powerful pressure-suction pump, offers eight selectable performance levels, adjustable flow rate distribution for internal/external circulation for optimal volume flow and pressure
- Ball bearing pump for extreme requirements: Guarantees safe operation with highly viscous and dense heat transfer fluids as well as with impurities in the temperature control bath.
- Easily accessible front switch on the control head allows the pump output to be adjusted during operation.
- Adaptive bath edge ventilation (patent application): - Prevents icing and condensation - Stops water entering the bath - Blocks vapors to protect electronics. To increase operational safety and extend service life.
- Extensive functionality with programmer, safe mode, calibration options, controller self-adaptation and weekly planner for precise and flexible process control.
- Wireless communication: Integrated WLAN enables effortless connection with PC, tablet and smartphone.
- Intelligent remote control and monitoring: Integrated web server allows flexible remote control in the company network via the LAUDA Command app or browser-based, secured by PKI and 2-factor authentication. The connection to LAUDA.LIVE enables global, cloud-based data analysis and remote maintenance.
- Maximum networking: Comprehensive connectivity for almost any application thanks to standard Ethernet, USB and interface for an external Pt100 as well as eleven optional interface modules.
- Comprehensive safety functions: - Effective over- and under-level protection - Adjustable overtemperature protection with acoustic alarm - Automatic system diagnostics at start-up with alarm and error message display - Smart temperature control media management with automatic limit value adjustment. For reliable operation and improved safety of your valuable samples.



Reserve technical changes

LAUDA DR. R. WOBSEY GMBH & CO. KG  
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0  
info@lauda.de • www.lauda.de  
WEEE-Reg.-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:  
LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
Sitz Lauda-Königshofen  
Registergericht Mannheim • HRB 560226

Geschäftsführer:  
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,  
Dr. Marc Stricker  
Beirat: Dr. Gerhard Wobser

## PRODUCT DATA SHEET

Published: 2026-07-21

LAUDA Universa U 8 M

Heating thermostat 100-125 V; 50/60 Hz

Part Number: L003871

### Options included

- Integrated Wi-Fi communication: The device may only be imported and used in certified countries and regions: United States of America, Canada, EU including the UK and Switzerland, and India.



Working temperature min.  
70 °C



Working temperature max.  
300 °C

Reserve technical changes

LAUDA DR. R. WOBSEY GMBH & CO. KG  
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0  
info@lauda.de • www.lauda.de  
WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:  
LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
Sitz Lauda-Königshofen  
Registergericht Mannheim • HRB 560226

Geschäftsführer:  
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,  
Dr. Marc Stricker  
Beirat: Dr. Gerhard Wobser

## PRODUCT DATA SHEET

Published: 2026-07-21

LAUDA Universa U 8 M

Heating thermostat 100-125 V; 50/60 Hz

Part Number: L003871

### Technical Features

|                                                 |                                                                                                                                               |
|-------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| Working temperature range                       | 70 ... 300 °C                                                                                                                                 |
| Working temperature range with external cooling | 20 ... 300 °C                                                                                                                                 |
| Operating temperature range                     | -30 ... 300 °C                                                                                                                                |
| Ambient temperature range                       | 5 ... 40 °C                                                                                                                                   |
| Temperature stability                           | 0.01 ± K                                                                                                                                      |
| Heating capacity range                          | 1.4 ... 2.0 kW                                                                                                                                |
| Power consumption max.                          | 2 kW                                                                                                                                          |
| Current max.                                    | 16 A                                                                                                                                          |
| Size of bath (W x D x H)                        | 150 x 150 x 200 mm                                                                                                                            |
| Bath opening (WxT)                              | 150 x 150 mm                                                                                                                                  |
| Bath volume min. / max.                         | 5.8 / 8.5 L                                                                                                                                   |
| Pump Pressure max.                              | 0,7 bar                                                                                                                                       |
| Pump suction max.                               | 0,4 bar                                                                                                                                       |
| Pump flow rate max. (pressure)                  | 25 L/min                                                                                                                                      |
| Pump Flow rate max. (suction)                   | 23 L/min                                                                                                                                      |
| In / Outlet connection thread (outside)         | M16 x 1                                                                                                                                       |
| In / Outlet Ø olives                            | 13 mm                                                                                                                                         |
| Overall dimensions (WxDxH)                      | 230 x 400 x 497 mm                                                                                                                            |
| Weight                                          | 18 kg                                                                                                                                         |
| Power supply                                    | 100-125 V; 50/60 Hz                                                                                                                           |
| Power plug                                      | Power cord with plug (NEMA 5-20P)                                                                                                             |
| Certification                                   | NRTL according to UL 61010-1:2012/R:2023-06, UL<br>61010-2-010:2019, CSA C22.2 No. 61010-1:2012/U3:2023-06, CSA<br>C22.2 No. 61010-2-010:2019 |

Reserve technical changes

LAUDA DR. R. WOBSEY GMBH & CO. KG  
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0  
info@lauda.de • www.lauda.de  
WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:  
LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
Sitz Lauda-Königshofen  
Registergericht Mannheim • HRB 560226

Geschäftsführer:  
Dr. Gunther Wobsey (Vors.), Dr. Mario Englert,  
Dr. Marc Stricker  
Beirat: Dr. Gerhard Wobsey

## PRODUCT DATA SHEET

Published: 2026-07-21

LAUDA Universa U 8 M

Heating thermostat 100-125 V; 50/60 Hz

Part Number: L003871



Power cord with plug (NEMA 5-20P)

### Standard accessories

- 1 Bath cover
- Pump connection set with M16x1 stainless steel connections
- Cooling coil with M16x1 stainless steel connections
- 2 hose olives 13.5 mm, 2 union nuts

LAUDA DR. R. WOBSEY GMBH & CO. KG  
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0  
info@lauda.de • www.lauda.de  
WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:  
LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
Sitz Lauda-Königshofen  
Registergericht Mannheim • HRB 560226

Geschäftsführer:  
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,  
Dr. Marc Stricker  
Beirat: Dr. Gerhard Wobser

## PRODUCT DATA SHEET

Published: 2026-07-21


LAUDA Universa U 8 M

Heating thermostat 100-125 V; 50/60 Hz

Part Number: L003871

### HEATING PERFORMANCE Heat transfer liquid: Silicone oil

Bath temperature °C



- 1 U 8 M
- 2 U 12 M
- 3 U 20 M
- 4 U 40 M

LAUDA DR. R. WOBSEY GMBH & CO. KG  
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0  
info@lauda.de • www.lauda.de  
WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:  
LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
Sitz Lauda-Königshofen  
Registergericht Mannheim • HRB 560226

Geschäftsführer:  
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,  
Dr. Marc Stricker  
Beirat: Dr. Gerhard Wobser

## PRODUCT DATA SHEET

Published: 2026-07-21


LAUDA Universa U 8 M

Heating thermostat 100-125 V; 50/60 Hz

Part Number: L003871

### PUMP CHARACTERISTIC Heat transfer liquid: Water

Pressure bar



- 1 Stage 1
- 2 Stage 2
- 3 Stage 3
- 4 Stage 4
- 5 Stage 5
- 6 Stage 6
- 7 Stage 7
- 8 Stage 8

Suction

Flow rate L/min

LAUDA DR. R. WOBSEY GMBH & CO. KG  
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0  
info@lauda.de • www.lauda.de  
WEEE-Reg.-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:  
LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
Sitz Lauda-Königshofen  
Registergericht Mannheim • HRB 560226

Geschäftsführer:  
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,  
Dr. Marc Stricker  
Beirat: Dr. Gerhard Wobser