

## PRODUCT DATA SHEET

Published: 2026-03-11

LAUDA Variocool VC 10000

Process thermostat 208-220 V; 60 Hz

Part Number: L004365

### Features

- Coloured TFT display for simultaneous indication of actual & set values and graphic illustration of the temperature profile
- Clear text menu navigation, six selectable languages DE, EN, FR, ES, IT, RU
- Easy input via cursor and soft keys
- Fully electronic continuous controller with PID action
- Electronic level indication and low level alarm
- Powerful pressure pump
- USB interface as standard
- Remote fault indication through floating contact
- Upgradeable with an interface module (analogue module, contact module, RS 232/485 module, Profibus, Ethernet-USB module)
- Integrated programmer with max. 150 segments, splittable in 5 programmes
- Adjustable bypass for pressure limiting
- Filler opening on top, drain tap on the backside
- SmartCool system for energy-saving digital cooling management including compressor on-off control
- Operates with non flammable liquids (water, water/glycol)
- Process thermostat suitable for use with non-flammable heat transfer liquids



Reserve technical changes



Working temperature min.  
-25 °C



Working temperature max.  
80 °C

LAUDA DR. R. WOBSEY GMBH & CO. KG  
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0  
info@lauda.de • www.lauda.de  
WEEE-Reg.-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:  
LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
Sitz Lauda-Königshofen  
Registergericht Mannheim • HRB 560226

Geschäftsführer:  
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,  
Dr. Marc Stricker  
Beirat: Dr. Gerhard Wobser

## PRODUCT DATA SHEET

Published: 2026-03-11

LAUDA Variocool VC 10000

Process thermostat 208-220 V; 60 Hz

Part Number: L004365

### Technical Features (according to DIN 12876)

Working temperature range	-25 ... 80 °C
Ambient temperature range	5 ... 40 °C
Temperature stability	0.1 ± K
Heater power max.	6.9 kW
Power consumption max.	8.1 kW
Current max.	24 A
Pump Pressure max.	5,0 bar
Pump flow rate max. (pressure)	60 L/min
In / Outlet connection thread (outside)	G 1 1/4"
Pressure adjustment	bypass
Filling volume min.	48 L
Filling volume max.	64 L
Overall dimensions (WxDxH)	650 x 670 x 1250 mm
Weight	155 kg
Refrigerant stage 1	R-513A (GWP 631); 2.000 kg; 1.3 t CO <sub>2</sub> -eq
Power supply	208-220 V; 3/PE; 60 Hz
Power plug	Power cord with plug (NEMA L16-30P twist lock; 30 A)

Reserve technical changes



Power cord with plug (NEMA L16-30P twist lock; 30 A)

LAUDA DR. R. WOBSEY GMBH & CO. KG  
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0  
info@lauda.de • www.lauda.de  
WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:  
LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
Sitz Lauda-Königshofen  
Registergericht Mannheim • HRB 560226

Geschäftsführer:  
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,  
Dr. Marc Stricker  
Beirat: Dr. Gerhard Wobser

## PRODUCT DATA SHEET

Published: 2026-03-11

LAUDA Variocool VC 10000

Process thermostat 208-220 V; 60 Hz

Part Number: L004365

Temperature	Heat transfer liquid	Cooling Capacity 60 Hz
20 °C	Ethanol	10 kW
10 °C	Ethanol	7.8 kW
0 °C	Ethanol	5.6 kW
-10 °C	Ethanol	3.7 kW
-20 °C	Ethanol	2 kW
-25 °C	Ethanol	1.35 kW

Reserve technical changes

LAUDA DR. R. WOBSEY GMBH & CO. KG  
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0  
info@lauda.de • www.lauda.de  
WEEE-Reg.-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:  
LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
Sitz Lauda-Königshofen  
Registergericht Mannheim • HRB 560226

Geschäftsführer:  
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,  
Dr. Marc Stricker  
Beirat: Dr. Gerhard Wobser

## PRODUCT DATA SHEET

Published: 2026-03-11


LAUDA Variocool VC 10000

Process thermostat 208-220 V; 60 Hz

Part Number: L004365

### PUMP CHARACTERISTIC Heat transfer liquid: Water

Pressure bar



- 1 0.9 bar, 28 L/min
- 2 3.2 bar, 37 L/min
- 3 4.8 bar, 37 L/min
- 4 5.0 bar, 60 L/min

Flow rate L/min

Reserve technical changes

LAUDA DR. R. WOBSEY GMBH & CO. KG  
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0  
info@lauda.de • www.lauda.de  
WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen  
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:  
LAUDA DR. R. WOBSEY Verwaltungs-GmbH  
Sitz Lauda-Königshofen  
Registergericht Mannheim • HRB 560226

Geschäftsführer:  
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,  
Dr. Marc Stricker  
Beirat: Dr. Gerhard Wobser