

PRODUCT DATA SHEET

Standing: 2023-02-24

LAUDA Varioshake VS 15 R

Shaker 230 V; 50/60 Hz

Part Number: L003060

Features

- Shaker with rocking motion, heavy-duty and low-noise, versatile
- Shaking frequency display and setting digitally via LC display, in steps of 0.5 rpm, gentle start-up
- The setpoint and actual values as well as the shaking frequency are displayed on two LC displays
- User-friendly microprocessor technology
- Membrane keyboard with distinctive symbols.
- Timer adjustable from 1 min. up to 99:59 hours or continuous operation
- Optional RS 232 interface on request
- Shaking table made of anodized aluminum with four plastic pins
- Drive by an overload-protected AC motor
- Compact, robust and low-wear mechanism
- Constant speed, independent of load
- Excellent for continuous use
- Outer housing made of electrolytically galvanized sheet steel, powder-coated



Technical Features

Ambient temperature range	10 ... 50 °C
Shaking tray (WxD)	450 x 450 mm
Shaking amplitude	3 °
Shaking frequency	2 ... 50 1/min
Load max.	15 kg
Overall dimensions (WxDxH)	480 x 487 x 160 mm
Weight	17 kg
Power plug	Power cord with angled plug (CEE7/7)
Power supply	230 V; 50/60 Hz

LAUDA DR. R. WOBSEY GMBH & CO. KG
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0 • F + 49 (0) 9343 503-222
info@lauda.de • www.lauda.de
WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:
LAUDA DR. R. WOBSEY Verwaltungs-GmbH
Sitz Lauda-Königshofen
Registergericht Mannheim • HRB 560226

Geschäftsführer:
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,
Dr. Ralf Hermann, Dr. Marc Stricker
Beirat: Dr. Gerhard Wobser