

PRODUCT DATA SHEET

Standing: 2023-02-24

LAUDA Varioshake VS 20 OH

Shaker 230 V; 50/60 Hz

Part Number: L003064

Features

- Shaker with overhead rotation, heavy duty, ideal for mixing powders and pasty samples
- Speed display
- Electronic speed control, stepless, gentle start-up
- Clear control panel for easy operation with rotary knobs
- Capacity at uniform loading: 12 vessels, round or square
- Vessels up to 110 mm Ø and 270 mm height, height adjustable clamp holders
- Drive by an overload-protected DC motor
- Compact, low-wear mechanism with mass balancing for a secure stand
- Rotating rack with ball bearings on both sides with safe drive via slide hub
- Height-adjustable holding devices made of stainless steel for safe, firm clamping of the vessels
- Constant speed, independent of load
- Excellent for continuous use
- Outer housing made of electrolytically galvanized sheet steel, powder-coated



Technical Features

Ambient temperature range	10 ... 40 °C
Power consumption max.	0.1 kW
Shaking frequency	1 ... 20 1/min
Load max.	20 kg
Overall dimensions (WxDxH)	770 x 700 x 715 mm
Weight	68 kg
Power plug	Power cord with angled plug (CEE7/7)
Power supply	230 V; 50/60 Hz

LAUDA DR. R. WOBSEY GMBH & CO. KG
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0 • F + 49 (0) 9343 503-222
info@lauda.de • www.lauda.de
WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:
LAUDA DR. R. WOBSEY Verwaltungs-GmbH
Sitz Lauda-Königshofen
Registergericht Mannheim • HRB 560226

Geschäftsführer:
Dr. Gunther Wobse (Vors.), Dr. Mario Englert,
Dr. Ralf Hermann, Dr. Marc Stricker
Beirat: Dr. Gerhard Wobse