

PRODUCT DATA SHEET

Published: 2025-10-27

LAUDA Varioshake VS 30 O

Shaker 230 V; 50 Hz

Part Number: L003298

Features

- Shaker with orbital motion, heavy duty, low noise, in a compact design
- Shaking frequency display and setting digitally via OLED display, in steps of 1.0 rpm, gentle start-up
- The setpoint and actual values as well as the shaking frequency are displayed on two LC displays
- User-friendly microprocessor technology
- Membrane keyboard with distinctive symbols.
- Timer adjustable from 1 min. up to 99:59 hours or continuous operation
- Four support rods and collars for secure attachment of accessories
- Special rubber mat for good adhesion of the objects on the shaking table
- Large shaking table made of electrolytically galvanized, powder-coated sheet steel
- Drive by an overload-protected AC motor
- Compact, low-wear mechanism with mass balancing for a secure stand
- Constant speed, independent of load
- Excellent for continuous use
- Outer housing made of electrolytically galvanized sheet steel, powder-coated



Options included

- Rack frame for doubling the capacity by accommodating two shaking trays; distance between trays = 205 mm
- The bottom tray can be loaded with flasks up to a max. of 500 ml
- The trays are not part of the delivery and have to be ordered separately

LAUDA DR. R. WOBSEY GMBH & CO. KG
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0
info@lauda.de • www.lauda.de
WEEE-Reg.-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:
LAUDA DR. R. WOBSEY Verwaltungs-GmbH
Sitz Lauda-Königshofen
Registergericht Mannheim • HRB 560226

Geschäftsführer:
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,
Dr. Marc Stricker
Beirat: Dr. Gerhard Wobser

PRODUCT DATA SHEET

Published: 2025-10-27


LAUDA Varioshake VS 30 O

Shaker 230 V; 50 Hz

Part Number: L003298

Technical Features

Ambient temperature range	10 ... 50 °C
Shaking platform (WxD)	676 x 540 mm
Power consumption max.	0.09 kW
Shaking amplitude	32 mm
Shaking frequency	20 ... 200 1/min
Load max.	30 kg
Overall dimensions (WxDxH)	705 x 607 x 445 mm
Weight	45 kg
Power plug	Power cord with angled plug (CEE7/7)
Power supply	230 V; 50 Hz



Power cord with angled plug (CEE7/7)

Reserve technical changes

LAUDA DR. R. WOBSEY GMBH & CO. KG
Laudaplatz 1 • 97922 Lauda-Königshofen • DE

T + 49 (0) 9343 503-0
info@lauda.de • www.lauda.de
WEEE-Reg-Nr.: DE 66 42 40 57

Kommanditgesellschaft: Sitz Lauda-Königshofen
Registergericht Mannheim • HRA 560069

Persönlich haftende Gesellschafterin:
LAUDA DR. R. WOBSEY Verwaltungs-GmbH
Sitz Lauda-Königshofen
Registergericht Mannheim • HRB 560226

Geschäftsführer:
Dr. Gunther Wobser (Vors.), Dr. Mario Englert,
Dr. Marc Stricker
Beirat: Dr. Gerhard Wobser